



eurosicma

CARE TECHNICAL DEPARTMENT




eurosicma

Forming and packaging machine for cotton swabs EURO P8

Fully electronic machine

Different configurations available

**High-performance machine
Speed up to 3000 pcs/min**



Quick change of size and parameter setting

PC-based technology

The standard version includes the following features:

- + Fusing or gluing unit for cotton anchorage
- + Turn table disc for manual collection of cotton swabs Mod BT

Model	Filled in by	Data	Approved by	Valid from	Release N.	Purpose
EURO P8	FV	31/1/2013	FR	1/2/2013	.1	Web download



eurosicma

CARE TECHNICAL DEPARTMENT




eurosicma

Configurations available



- Plastic box application:**
- Infeed unit driven by brushless motors
 - Electronically synchronised with the EURO P8
 - Automatic application of the lids

- Carton box application:**
- Dedicated supports to carry the pre-shaped carton boxes
 - Shuttle device to have compacted layers



- Plastic round canister application:**
- Pick-up robot with brushless motor to fill the canister
 - Automatic application of the lids

Model	Filled in by	Data	Approved by	Valid from	Release N.	Purpose
EURO P8	FV	31/1/2013	FR	1/2/2013	.1	Web download



eurosicma

LINES TECHNICAL DEPARTMENT



eurosicma

Products and size range



- Traditional cotton swabs
- Baby safety cotton swabs
- Cosmetic cotton swabs
- Many more...

PRODUCT SIZE RANGE			
	Length mm	Weight g/m	Diameter mm
Cotton rope	min. 10 max. 30 **	min. 1,4 max. 4 ***	/
Stick dimension	min. 73 max. 76 +/- 0,5	/	min. 2,4 max. 2,8

** Depending on the rope material (cotton or synthetic rope)

*** Depending on the kinds of cotton swabs (standard, beauty, safety)

*The above data are strictly referred to standard applications.

*For specific data and changing size parts contact us at care@eurosicma.it

Model	Filled in by	Data	Approved by	Valid from	Release N.	Purpose
Euro P8	FV	31/1/2013	FR	1/2/2013	.1	Web download